

POWER SCOPE[®] 2




NEW ALTERNATE ATTACHMENT NUT

Closed channel alternate attachment nut allows for extraoral installation and wire is fully encapsulated.

CLASS II CORRECTION SIMPLIFIED

PowerScope 2 delivers simple, efficient Class II correction like you've never seen before. The latest generation of PowerScope features a stronger wire attachment nut and visual activation indicators.

- Fixed one-piece, one-size-fits-all design
- Easy chairside wire-to-wire installation
- No lab setup required
- No headgear or special band assemblies
- Use with banded or bondable molar tubes
- World-class clinical results



MAGNETIC FEATURE

Magnetic sleeve slides onto driver for secure hold of appliance during installation.



FEATURES AND BENEFITS

- One-size-fits-all Class II corrector for simple treatment application and easy inventory management
- One-piece, no assembly required, and no need for lab setup
- Internal NiTi spring mechanism delivers 260 grams of force during treatment
- Connects wire-to-wire for quick and easy chairside installation
- Can be used with both bondable or banded molar tubes
- No molar headgear tube required
- Telescoping mechanism will not disengage during treatment, helping avoid emergency visits
- Unique ball and socket joint for unrestricted movement and patient comfort
- Fatigue tested to ensure durability during treatment
- Can be used for unilateral or bilateral correction
- Works with fully bonded cases
- Crimpable shims available for activation of spring during treatment
- Open Channel or Closed Channel Nut Options

POWERSCOPE KITS

852-016537 1 Patient Kit
(Includes: 1 Right/1 Left with open channel nuts – *does not include Shims, Driver, or Magnets*)

852-016538 5 Patient Kit
(Includes: 5 Right/5 Left with Open Channel Nuts, 10 each 1 mm, 2 mm & 3 mm Crimpable Shims, 5 Right/5 Left Closed Channel Nuts, 1 Hex Head Driver, and 5 Driver Magnets)

POWERSCOPE ACCESSORIES

852-016539 PowerScope 2 — Right Arm (18 mm with open channel nuts)
852-016540 PowerScope 2 — Left Arm (18 mm with open channel nuts)
852-016541 Open Channel Attachment Nuts — 10 pack (5 right and 5 left)
852-030576 Closed Channel Attachment Nuts — 10 pack (5 right and 5 left)
852-026533 Driver Magnets — 5 pack
855-733 Crimpable Shims 1 mm — 10 pack
855-728 Crimpable Shims 2 mm — 10 pack
855-738 Crimpable Shims 3 mm — 10 pack
855-515 Hex Head Driver



3524 Washington Avenue
Sheboygan, Wisconsin, 53081 USA

Phone: +1 920 457 5051
 Email: cs@americanortho.com
 Web: americanortho.com



©2020 American Orthodontics Corporation
All Rights Reserved

FOLLOW US ON

